

GP2E06 Cut Sheet



Schneider Electric Easy TeSys series manual motor protector, pushbutton, 1.6A, thermal overload, 1-1.6 adjustable, 22.5A instantaneous trip rating, 45mm frame.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GP2E06>

Technical Specifications

Brand	Schneider Electric
Series	Easy TeSys
Item	Motor protector
Starter Type	Manual
Actuator Type	Pushbutton
Amperage Rating	1.6A
Voltage Rating	600 VAC
Horsepower Rating	3/4hp
Relay Type	Thermal overload
Operation Type	Bi-metallic
Full Load Amperage Range	1-1.6 adjustable

Instantaneous Trip Rating	22.5A
Number of Poles	3
Power Poles	(3) N.O.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
SCCR Rating	35kA SCCR
UL Rating	UL 60947-4-1
Frame	45mm
Mounting	35mm DIN rail
Connection	Screw terminal

Agency Approvals

UL Listed File #	E89451
CE	View CE declarations
CSA File #	164581
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GP2E06.pdf>
See store item page for other formats.