

GP2E10 Cut Sheet



Schneider Electric Easy TeSys series manual motor protector, pushbutton, 6.3A, thermal overload, 4-6.3 adjustable, 78A instantaneous trip rating, 45mm frame.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GP2E10>

Technical Specifications

Brand	Schneider Electric
Series	Easy TeSys
Item	Motor protector
Starter Type	Manual
Actuator Type	Pushbutton
Amperage Rating	6.3A
Voltage Rating	600 VAC
Horsepower Rating	3hp
Relay Type	Thermal overload
Operation Type	Bi-metallic
Full Load Amperage Range	4-6.3 adjustable

Instantaneous Trip Rating	78A
Number of Poles	3
Power Poles	(3) N.O.
Trip Class	Trip Class 10
Phase Loss Sensitive	Yes
Ground Fault Protection	No
SCCR Rating	35kA SCCR
UL Rating	UL 60947-4-1
Frame	45mm
Mounting	35mm DIN rail
Connection	Screw terminal

Agency Approvals

UL Listed File #	E89451
CE	View CE declarations
CSA File #	164581
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GP2E10.pdf>
See store item page for other formats.