

# GQ-50-60-A-1-4 Cut Sheet



Gefran solid state relay, panel mount, 20-260 VAC input voltage, SPST, (1) N.O. SCR, 50A contact rating, 48-600 VAC load voltage, push-in spring, overvoltage protection. Thermal mounting pad included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GQ-50-60-A-1-4>

## Technical Specifications

<b>Brand</b>	Gefran
<b>Item</b>	Relay
<b>Relay Type</b>	Solid state
<b>Mounting</b>	Panel
<b>Relay Housing Type</b>	Finger-safe hockey puck
<b>Input Voltage</b>	20-260 VAC
<b>Relay Configuration</b>	SPST
<b>Output Type</b>	(1) N.O. SCR

<b>Load Voltage</b>	48-600 VAC
<b>Contact Rating</b>	50A
<b>Switching Type</b>	Zero cross
<b>Connector Type</b>	Push-in spring
<b>Indicator</b>	LED
<b>Protection Type(s)</b>	overvoltage
<b>Includes</b>	Thermal mounting pad

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E243386
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/GQ-50-60-A-1-4.pdf>  
See store item page for other formats.