

GQ-75-60-D-1-3 Cut Sheet



Gefran solid state relay, panel mount, 3-32 VDC input voltage, SPST, (1) N.O. SCR, 75A contact rating, 48-600 VAC load voltage, screw terminal(s), overvoltage protection. Thermal mounting pad included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GQ-75-60-D-1-3>

Technical Specifications

Brand	Gefran
Item	Relay
Relay Type	Solid state
Mounting	Panel
Relay Housing Type	Finger-safe hockey puck
Input Voltage	3-32 VDC
Relay Configuration	SPST
Output Type	(1) N.O. SCR

Load Voltage	48-600 VAC
Contact Rating	75A
Switching Type	Zero cross
Connector Type	Screw terminal(s)
Indicator	LED
Protection Type(s)	overvoltage
Includes	Thermal mounting pad

Agency Approvals

UL Listed File #	None
UL Recognized File #	E243386
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GQ-75-60-D-1-3.pdf>
See store item page for other formats.