

GR-REC2-USB-2A Cut Sheet



Gladiator (2) straight blade and (2) USB Type A receptacle, 15A, 125 VAC, 1-phase, 2-pole, 3-wire, nylon housing, panel or 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GR-REC2-USB-2A>

Technical Specifications

| | |
|---------------------------|---------------------------------------|
| Brand | Gladiator |
| Item | Receptacle |
| Receptacle Type | Quad |
| Wiring Device Type | (2) straight blade and (2) USB Type A |
| Self-grounding | No |
| Amperage Rating | 15A |
| Voltage Rating | 125 VAC |
| Number of Phases | 1 |
| Number of Poles | 2 |

| | |
|-------------------------------|---|
| Number of Wires | 3 |
| Wire Size | 14-12 AWG solid or stranded |
| Copper Wire Only | Yes |
| Configuration | NEMA 5-15 |
| Housing Material | Nylon |
| Mounting | Panel or 35mm DIN rail |
| Color | Black |
| Additional Information | For laptop computers and test equipment |

Agency Approvals

| | |
|-----------------------------|------------------------|
| UL Listed File # | E551575 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GR-REC2-USB-2A.pdf>
See store item page for other formats.