

# GR-REC2 Cut Sheet



Gladiator (2) straight blade receptacle, 15A, 125 VAC, 1-phase, 2-pole, 3-wire, nylon housing, panel or 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GR-REC2>

## Technical Specifications

<b>Brand</b>	Gladiator
<b>Item</b>	Receptacle
<b>Receptacle Type</b>	Duplex
<b>Wiring Device Type</b>	(2) straight blade
<b>Self-grounding</b>	No
<b>Amperage Rating</b>	15A
<b>Voltage Rating</b>	125 VAC
<b>Number of Phases</b>	1
<b>Number of Poles</b>	2

<b>Number of Wires</b>	3
<b>Wire Size</b>	14-12 AWG solid or stranded
<b>Copper Wire Only</b>	Yes
<b>Configuration</b>	NEMA 5-15
<b>Housing Material</b>	Nylon
<b>Mounting</b>	Panel or 35mm DIN rail
<b>Color</b>	Black
<b>Additional Information</b>	For laptop computers and test equipment

## Agency Approvals

<b>UL Listed File #</b>	E551575
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/GR-REC2.pdf>  
See store item page for other formats.