

GR-USB-4A Cut Sheet



Gladiator (4) USB Type A receptacle, 15A, 125 VAC, 1-phase, 2-pole, 3-wire, nylon housing, panel or 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GR-USB-4A>

Technical Specifications

Brand	Gladiator
Item	Receptacle
Receptacle Type	Quad
Wiring Device Type	(4) USB Type A
Self-grounding	No
Amperage Rating	15A
Voltage Rating	125 VAC
Number of Phases	1

Number of Poles	2
Number of Wires	3
Wire Size	14-12 AWG solid or stranded
Copper Wire Only	Yes
Housing Material	Nylon
Mounting	Panel or 35mm DIN rail
Color	Black
Additional Information	For laptop computers and test equipment

Agency Approvals

UL Listed File #	E551575
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GR-USB-4A.pdf>
See store item page for other formats.