

# GS-3DBU Cut Sheet



DURApulse dynamic braking unit, 30 kW, 460 VAC, IP50, built-in temperature switch. For use with DURApulse AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GS-3DBU>

## Technical Specifications

Brand	DURApulse
Item	Dynamic braking unit
Brake Resistor Power Rating	30 kW
Voltage Rating	460 VAC
IP Rating	IP50
Built-in Temperature Switch	Yes
For Use With	DURApulse AC drives

## Agency Approvals

UL Recognized File #	E198015
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GS-3DBU.pdf>  
See store item page for other formats.