

GS-7DBU Cut Sheet



DURApulse dynamic braking unit, 185 kW, 460 VAC, IP10, built-in temperature switch. For use with DURApulse AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GS-7DBU>

Technical Specifications

Brand	DURApulse
Item	Dynamic braking unit
Brake Resistor Power Rating	185 kW
Voltage Rating	460 VAC
IP Rating	IP10
Built-in Temperature Switch	Yes
For Use With	DURApulse AC drives

Agency Approvals

UL Recognized File #	E198015
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GS-7DBU.pdf>
See store item page for other formats.