

GS20A-CAPF Cut Sheet



DURApulse EMI capacitive filter, 110-480 VAC, 3-phase, panel mount, EMI/RFI filtering, drive rated, basic, pigtail with wire leads. For use with GS10, GS20 and GS20X series AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GS20A-CAPF>

Technical Specifications

Brand	DURApulse
Item	Capacitive filter
Filter Type	EMI
Filter Voltage Rating	110-480 VAC
Number of Input Phases	3
On/Off Switch	No
Fused	No
Mounting	Panel
Filtering	EMI/RFI
Filter Application	Drive rated
Filter Performance Level	Basic
Connector Type	Pigtail with wire leads
For Use With	GS10, GS20 and GS20X series AC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	E197592
UL Hazardous File #	None
CE	View CE declarations
CSA File #	none
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GS20A-CAPF.pdf>
See store item page for other formats.