

GS30A-02TRC Cut Sheet



DURApulse GS30 series relay output module, 2-point, 240 VAC/30 VDC, (2) Form C (SPST) relays, 2 isolated common(s), 1 point(s) per common. Screw terminal blocks included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GS30A-02TRC>

Technical Specifications

Brand	DURApulse
Item	Output module
I/O Module Type	Relay
Series	GS30
Number of Output Points	2
Nominal Output Voltage	240 VAC/30 VDC
Relay Configuration	(2) Form C (SPST) relays
Number of Isolated Commons	2

Jumper Selectable Isolation	No
Number of Points per Common	1
Inductive Output Current	1.2A
Resistive Output Current	5A
Fuse Type	User-supplied external fuse
Includes	Screw terminal blocks

Agency Approvals

UL Listed File #	E176972
UL Recognized File #	E198015
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GS30A-02TRC.pdf>
See store item page for other formats.