


GS30A-CM-ECAT Cut Sheet



DURApulse GS30 series communication module, EtherCAT CoE protocol, 2 ports, (2) Ethernet (RJ45) port(s). For use with GS30 series AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GS30A-CM-ECAT>

Technical Specifications

Brand	DURApulse
Item	Communication module
Series	GS30
Number of Ports	2
Buffered Ports	No
Communication Port and Connection Type(s)	(2) Ethernet (RJ45)
Port Protocol(s)	EtherCAT CoE Slave protocol
Port Speed(s)	100 Mbps auto-detect
For Use With	GS30 series AC drives

Agency Approvals

UL Listed File #	E176972
UL Recognized File #	E198015
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GS30A-CM-ECAT.pdf>
See store item page for other formats.