


GS30A-CM-EIP1 Cut Sheet



DURApulse GS30 series communication module, EtherNet/IP and Modbus TCP, 1 port, (1) Ethernet (RJ45) port(s). For use with GS30 series AC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GS30A-CM-EIP1>

Technical Specifications

Brand	DURApulse
Item	Communication module
Series	GS30
Number of Ports	1
Buffered Ports	No
Communication Port and Connection Type(s)	(1) Ethernet (RJ45)
Port Protocol(s)	<ul style="list-style-type: none">• EtherNet/IP Server• Modbus TCP Server
Port Speed(s)	10/100 Mbps auto-detect
For Use With	GS30 series AC drives

Agency Approvals

UL Listed File #	E176972
UL Recognized File #	E198015
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/GS30A-CM-EIP1.pdf>
See store item page for other formats.