


GSD7-240-1CR3 Cut Sheet



IronHorse GSD7 series DC reversing drive, 240 VAC, 1-phase, 1/25 to 1/4hp at 180 VDC, 1.2A, open frame, panel mount, built-in reverse, maximum 3 reverses/minute, potentiometer input, SCR output.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GSD7-240-1CR3>

Technical Specifications

Brand	IronHorse
Item	Drive
Controller Type	Reversing
Series	GSD7
Voltage Type	DC
Number of Input Phases	1
Nominal Drive Input Voltage	240 VAC
Nominal Drive Output Voltage	Output up to 180 VDC
Horsepower by Voltage	1/25 to 1/4hp at 180 VDC
Amperage Rating	1.2A
Variable Torque Amperage Rating	500 mA - 1.2A
Control Mode	DC
Safe Torque Off (STO)	No
Temperature Rating	-10 to 45 deg C

Enclosure Type	Open frame
IP Rating	IP00
Mounting	Panel
Input Signal	Potentiometer input
On/Off Switch	No
Shunt Field Supply	Yes
Output Type	SCR output
Reverse Capability	Built-in
Reverse Cycle Frequency	Maximum 3 reverses/minute
Output Frequency Range	DC
Connector Type	Screw terminals
SCCR Rating	SCCR exempt
For Use With	Permanent magnet DC, shunt wound DC and universal motors
Includes	Speed potentiometer with knob and 0-100% faceplate

Agency Approvals

UL Listed File #	E333109
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document