

GSDA-DP-D Cut Sheet



IronHorse GSD series PID digital potentiometer, 120/240 VAC input, voltage, NEMA 4X, IP67, aluminum housing. For use with multiple AC and DC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GSDA-DP-D>

Technical Specifications

Brand	IronHorse
Item	PID digital potentiometer
Series	GSD
Replacement	No
Input Voltage Rating	120/240 VAC
Output Signal Type	Voltage
Enclosure Type	NEMA 4X
IP Rating	IP67
Housing Material	Aluminum
Mounting	1/8 DIN
Connector Type	12-position terminal block
Terminal Block Type	Screw terminals
For Use With	Multiple AC and DC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document