

GSDA-DP-S Cut Sheet



IronHorse signal conditioner, isolated, current or voltage input, current or voltage output, 120/240 VAC operating voltage, IP67, 1/8 DIN mount, screw terminals.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GSDA-DP-S>

Technical Specifications

Brand	IronHorse
Item	Signal conditioner
Isolation	Isolated
Field Configurable	Yes
Input Current Signal Range	4-20 mA
Input Voltage Signal Range	0-10 VDC
Output Current Signal Range	4-20 mA
Output Voltage Signal Range	0-5 VDC and 0-20 VDC
Operating Voltage	120/240 VAC
Housing Material	Aluminum
IP Rating	IP67
Mounting	1/8 DIN
Electrical Connection	Screw terminals

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document