

GSDA-DP Cut Sheet



IronHorse GSD series digital potentiometer, 120/240 VAC input, bipolar/unipolar, NEMA 4X, aluminum housing. For use with multiple AC and DC drives.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GSDA-DP>

Technical Specifications

Brand	IronHorse
Item	Digital potentiometer
Series	GSD
Replacement	No
Input Voltage Rating	120/240 VAC
Output Signal Type	Bipolar/unipolar
Enclosure Type	NEMA 4X
Housing Material	Aluminum
Mounting	1/8 DIN
Connector Type	12-position terminal block
Terminal Block Type	Screw terminals
For Use With	Multiple AC and DC drives

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document