

GVP-3C2P-PB Cut Sheet



NITRA pneumatic manual valve, 3-port (3-way), 2-position, N.C., pushbutton, spring return, 90-degree ports, 1/4in push-to-connect inlet(s), 1/4in push-to-connect outlet(s), (1) vent hole exhaust(s), Cv=0.29, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVP-3C2P-PB>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air or inert gas
Valve Type	Manual directional control
Port Quantity	3-port (3-way)
Number Of Positions	2
Valve Configuration	N.C.
Operator Type	Pushbutton
Action	Spring return
Body Material	Anodized aluminum
Mounting	Through panel
Inlet Port	1/4in push-to-connect

Outlet Port	1/4in push-to-connect
Exhaust Port	(1) vent hole
Port Orientation	90-degree
Stackable	No
Flow Coefficient	0.29
Maximum Operating Pressure	125 psi
Minimum Operating Pressure	0 psi
Form Factor	Standard
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GVP-3C2P-PB.pdf>
See store item page for other formats.