

# GVS-231F-TD Cut Sheet



NITRA pneumatic manual valve, 2-way, 3-position, center closed, toggle style actuator, detented, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), Cv=0.54, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVS-231F-TD>

## Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air or inert gas
Valve Type	Manual directional control
Port Quantity	2-way
Number Of Positions	3
Valve Configuration	Center closed
Operator Type	Toggle style actuator
Action	Detented
Body Material	Anodized aluminum

Mounting	Through panel
Inlet Port	1/8in female NPT
Outlet Port	1/8in female NPT
Stackable	No
Flow Coefficient	0.54
Maximum Operating Pressure	125 psi
Minimum Operating Pressure	0 psi
Includes	Mounting hardware

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GVS-231F-TD.pdf>  
See store item page for other formats.