

GVS-231F-TM Cut Sheet



NITRA manual valve, 2-way, 3-position, center closed, toggle style actuator, spring return, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), Cv=0.54, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVS-231F-TM>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air
Valve Type	Manual directional control
Port Quantity	2-way
Number Of Positions	3
Valve Configuration	Center closed
Operator Type	Toggle style actuator
Action	Spring return
Body Material	Anodized aluminum
Mounting	Through panel
Inlet Port	1/8in female NPT
Outlet Port	1/8in female NPT
Stackable	No
Flow Coefficient	0.54
Maximum Operating Pressure	125 psi
Minimum Operating Pressure	0 psi
Form Factor	Standard
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document