

GVS-331F-TM Cut Sheet



NITRA pneumatic manual valve, 3-port (3-way), 3-position, center exhaust, toggle style actuator, spring return, 1/8in female NPT inlet(s), 1/8in female NPT outlet(s), (1) vent hole exhaust(s), Cv=0.54, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVS-331F-TM>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air or inert gas
Valve Type	Manual directional control
Port Quantity	3-port (3-way)
Number Of Positions	3
Valve Configuration	Center exhaust
Operator Type	Toggle style actuator
Action	Spring return
Body Material	Anodized aluminum
Mounting	Through panel

Inlet Port	1/8in female NPT
Outlet Port	1/8in female NPT
Exhaust Port	(1) vent hole
Stackable	No
Flow Coefficient	0.54
Maximum Operating Pressure	125 psi
Minimum Operating Pressure	0 psi
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/GVS-331F-TM.pdf>
See store item page for other formats.