

# GVS-3C0F-TD-SS Cut Sheet



NITRA pneumatic manual valve, 3-port (3-way), 2-position, N.C., toggle style actuator, detented, 90-degree ports, #10-32 female UNF inlet(s), #10-32 female UNF outlet(s), #10-32 female threaded exhaust(s), Cv=0.27, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVS-3C0F-TD-SS>

## Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air or inert gas
Valve Type	Manual directional control
Port Quantity	3-port (3-way)
Number Of Positions	2
Valve Configuration	N.C.
Operator Type	Toggle style actuator
Action	Detented
Body Material	Stainless steel
Mounting	Through panel

Inlet Port	#10-32 female UNF
Outlet Port	#10-32 female UNF
Exhaust Port	#10-32 female threaded
Port Orientation	90-degree
Stackable	No
Flow Coefficient	0.27
Maximum Operating Pressure	125 psi
Minimum Operating Pressure	-26in Hg
Includes	Mounting hardware

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/GVS-3C0F-TD-SS.pdf>  
See store item page for other formats.