

# GVS-520F-PB Cut Sheet



NITRA manual valve, 5-port (4-way), 2-position, pushbutton, spring return, #10-32 female threaded inlet(s), #10-32 female threaded outlet(s), #10-32 female threaded exhaust(s), Cv=0.23, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVS-520F-PB>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Valve
<b>Working Fluid</b>	Air
<b>Valve Type</b>	Manual directional control
<b>Port Quantity</b>	5-port (4-way)
<b>Number Of Positions</b>	2
<b>Operator Type</b>	Pushbutton
<b>Action</b>	Spring return
<b>Body Material</b>	Anodized aluminum
<b>Mounting</b>	Through panel
<b>Inlet Port</b>	#10-32 female threaded
<b>Outlet Port</b>	#10-32 female threaded
<b>Exhaust Port</b>	#10-32 female threaded
<b>Stackable</b>	No
<b>Flow Coefficient</b>	0.23
<b>Maximum Operating Pressure</b>	126 psi
<b>Minimum Operating Pressure</b>	0 psi
<b>Form Factor</b>	Standard
<b>Includes</b>	Mounting hardware

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>