

GVS-520F-TD Cut Sheet



NITRA manual valve, 5-port (4-way), 2-position, toggle style actuator, detented, #10-32 female threaded inlet(s), #10-32 female threaded outlet(s), #10-32 female threaded exhaust(s), Cv=0.23, through panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/GVS-520F-TD>

Technical Specifications

Brand	NITRA
Item	Valve
Working Fluid	Air
Valve Type	Manual directional control
Port Quantity	5-port (4-way)
Number Of Positions	2
Operator Type	Toggle style actuator
Action	Detented
Body Material	Anodized aluminum
Mounting	Through panel
Inlet Port	#10-32 female threaded
Outlet Port	#10-32 female threaded
Exhaust Port	#10-32 female threaded
Stackable	No
Flow Coefficient	0.23
Maximum Operating Pressure	127 psi
Minimum Operating Pressure	0 psi
Form Factor	Standard
Includes	Mounting hardware

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document