

H11131202-1 Cut Sheet



Helukabel portable cord, unshielded, SJOOW, 300V, 2 conductors, 12 AWG, EPDM thermoset rubber conductor insulation material, black and white, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H11131202-1>

Technical Specifications

Brand	Helukabel
Item	Cord
Wire/Cable Type	Portable
UL Wire/Cable Type	SJOOW
Applicable Standards	UL 62, CSA Std. C22.2 No. 49 and MSHA
Application	General purpose
Flexibility	Flexible
Voltage Rating	300V
Conductors	2 conductors
Conductor Size	12 AWG
Conductor Stranding	65-stranded
Conductor Material	Bare copper
Conductor Insulation Material	EPDM thermoset rubber

Conductor Insulation Color	Black and white
Shielding	Unshielded
Jacket Material	CPE thermoset rubber
Jacket Color	Black
Nominal Overall Cable Diameter	0.41in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 50ft = Coil• 51 to 230ft = 14 x 7in Reel• 231 to 330ft = 14 x 10in Reel• 331 to 510ft = 16 x 10in Reel• 511 to 710ft = 18 x 10in Reel• 711 to 925ft = 18 x 13in Reel• 926 to 1000ft = 24 x 17in Wooden Reel

Agency Approvals

UL Listed File #	E192384
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	View CE declarations
CSA File #	LL602586
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document