

# H11131204-1 Cut Sheet



Helukabel portable cord, unshielded, SJOOW, 300V, 4 conductors (includes ground), 12 AWG, EPDM thermoset rubber conductor insulation material, black, white, red and green, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H11131204-1>

## Technical Specifications

|                                      |                                       |
|--------------------------------------|---------------------------------------|
| <b>Brand</b>                         | Helukabel                             |
| <b>Item</b>                          | Cord                                  |
| <b>Wire/Cable Type</b>               | Portable                              |
| <b>UL Wire/Cable Type</b>            | SJOOW                                 |
| <b>Applicable Standards</b>          | UL 62, CSA Std. C22.2 No. 49 and MSHA |
| <b>Application</b>                   | General purpose                       |
| <b>Flexibility</b>                   | Flexible                              |
| <b>Voltage Rating</b>                | 300V                                  |
| <b>Conductors</b>                    | 4 conductors (includes ground)        |
| <b>Conductor Size</b>                | 12 AWG                                |
| <b>Conductor Stranding</b>           | 65-stranded                           |
| <b>Conductor Material</b>            | Bare copper                           |
| <b>Conductor Insulation Material</b> | EPDM thermoset rubber                 |

|                                       |   |
|---------------------------------------|---|
| <b>Conductor Insulation Color</b>     | Black, white, red and green   |
| <b>Shielding</b>                      | Unshielded  |
| <b>Jacket Material</b>                | CPE thermoset rubber  |
| <b>Jacket Color</b>                   | Black   |
| <b>Nominal Overall Cable Diameter</b> | 0.47in  |
| <b>Bulk Length</b>                    | Cut to length   |
| <b>Package Type</b>                   | <ul style="list-style-type: none"><li>• 20 to 50ft = Coil</li><li>• 51 to 175ft = 14 x 7in Reel</li><li>• 176 to 250ft = 14 x 10in Reel</li><li>• 251 to 385ft = 16 x 10in Reel</li><li>• 386 to 540ft = 18 x 10in Reel</li><li>• 541 to 705ft = 18 x 13in Reel</li><li>• 706 to 1000ft = 24 x 17in Wooden Reel</li></ul> |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E192384                                |
| <b>UL Recognized File #</b> | N/A                                    |
| <b>UL Hazardous File #</b>  | N/A                                    |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LL602586                               |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |