

H11131402-1 Cut Sheet



Helukabel portable cord, unshielded, SJOOW, 300V, 2 conductors, 14 AWG, EPDM thermoset rubber conductor insulation material, black and white, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H11131402-1>

Technical Specifications

| | |
|--------------------------------------|---------------------------------------|
| Brand | Helukabel |
| Item | Cord |
| Wire/Cable Type | Portable |
| UL Wire/Cable Type | SJOOW |
| Applicable Standards | UL 62, CSA Std. C22.2 No. 49 and MSHA |
| Application | General purpose |
| Flexibility | Flexible |
| Voltage Rating | 300V |
| Conductors | 2 conductors |
| Conductor Size | 14 AWG |
| Conductor Stranding | 41-stranded |
| Conductor Material | Bare copper |
| Conductor Insulation Material | EPDM thermoset rubber |

| | |
|---------------------------------------|--|
| Conductor Insulation Color | Black and white |
| Shielding | Unshielded |
| Jacket Material | CPE thermoset rubber |
| Jacket Color | Black |
| Nominal Overall Cable Diameter | 0.34in |
| Bulk Length | Cut to length |
| Package Type | <ul style="list-style-type: none">• 20 to 75ft = Coil• 76 to 335ft = 14 x 7in Reel• 336 to 480ft = 14 x 10in Reel• 481 to 740ft = 16 x 10in Reel• 741 to 1000ft = 18 x 10in Reel |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E192384 |
| UL Recognized File # | N/A |
| UL Hazardous File # | N/A |
| CE | View CE declarations |
| CSA File # | LL602586 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |