

H11131602-1 Cut Sheet



Helukabel portable cord, unshielded, SJOOW, 300V, 2 conductors, 16 AWG, EPDM thermoset rubber conductor insulation material, black and white, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H11131602-1>

Technical Specifications

Brand	Helukabel
Item	Cord
Wire/Cable Type	Portable
UL Wire/Cable Type	SJOOW
Applicable Standards	UL 62, CSA Std. C22.2 No. 49 and MSHA
Application	General purpose
Flexibility	Flexible
Voltage Rating	300V
Conductors	2 conductors
Conductor Size	16 AWG
Conductor Stranding	26-stranded
Conductor Material	Bare copper
Conductor Insulation Material	EPDM thermoset rubber

Conductor Insulation Color	Black and white
Shielding	Unshielded
Jacket Material	CPE thermoset rubber
Jacket Color	Black
Nominal Overall Cable Diameter	0.31in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 99ft = Coil• 100 to 405ft = 14 x 7in Reel• 406 to 580ft = 14 x 10in Reel• 581 to 890ft = 16 x 10in Reel• 891 to 1000ft = 18 x 10in Reel

Agency Approvals

UL Listed File #	E192384
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	View CE declarations
CSA File #	LL602586
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document