

# H11160803-1 Cut Sheet



Helukabel portable cord, unshielded, SOOW, 600V, 3 conductors (includes ground), 8 AWG, EPDM thermoset rubber conductor insulation material, black, white and green, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H11160803-1>

## Technical Specifications

<b>Brand</b>	Helukabel
<b>Item</b>	Cord
<b>Wire/Cable Type</b>	Portable
<b>UL Wire/Cable Type</b>	SOOW
<b>Applicable Standards</b>	UL 62, CSA Std. C22.2 No. 49 and MSHA
<b>Application</b>	Power
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	600V
<b>Conductors</b>	3 conductors (includes ground)
<b>Conductor Size</b>	8 AWG
<b>Conductor Stranding</b>	168-stranded
<b>Conductor Material</b>	Bare copper
<b>Conductor Insulation Material</b>	EPDM thermoset rubber
<b>Conductor Insulation Color</b>	Black, white and green

<b>Shielding</b>	Unshielded
<b>Jacket Material</b>	CPE thermoset rubber
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.874in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 1 to 30ft = Coil</li><li>• 31 to 50ft = 14 x 7in Reel</li><li>• 51 to 75ft = 14 x 10in Reel</li><li>• 76 to 110ft = 16 x 10in Reel</li><li>• 111 to 155ft = 18 x 10in Reel</li><li>• 156 to 205ft = 18 x 13in Reel</li><li>• 206 to 455ft = 24 x 17in Wooden Reel</li><li>• 456 to 725ft = 30 x 17in Wooden Reel</li><li>• 726 to 1000ft = Large Wooden Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E192384
<b>UL Recognized File #</b>	N/A
<b>UL Hazardous File #</b>	N/A
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	LL602586
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>