

H11161804-1 Cut Sheet



Helukabel portable cord, unshielded, SOOW, 600V, 4 conductors (includes ground), 18 AWG, EPDM thermoset rubber conductor insulation material, black, white, red and green, CPE thermoset rubber jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H11161804-1>

Technical Specifications

Brand	Helukabel
Item	Cord
Wire/Cable Type	Portable
UL Wire/Cable Type	SOOW
Applicable Standards	UL 62, CSA Std. C22.2 No. 49 and MSHA
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V
Conductors	4 conductors (includes ground)
Conductor Size	18 AWG
Conductor Stranding	16-stranded
Conductor Material	Bare copper
Conductor Insulation Material	EPDM thermoset rubber

Conductor Insulation Color	Black, white, red and green
Shielding	Unshielded
Jacket Material	CPE thermoset rubber
Jacket Color	Black
Nominal Overall Cable Diameter	0.39in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 50ft = Coil• 51 to 255ft = 14 x 7in Reel• 256 to 365ft = 14 x 10in Reel• 366 to 560ft = 16 x 10in Reel• 561 to 785ft = 18 x 10in Reel• 786 to 1000ft = 18 x 13in Reel

Agency Approvals

UL Listed File #	E192384
UL Recognized File #	N/A
UL Hazardous File #	N/A
CE	View CE declarations
CSA File #	LL602586
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document