

H12106HFNL-P10 Cut Sheet



Integra Premium series enclosure, NEMA 1/2/3/3R/3S/4/4X/12/13, 12 x 10 x 6in (HxWxD), wall mount, polycarbonate, light gray, gloss finish, single-door, glass-filled nylon quick-release latch, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H12106HFNL-P10>

Technical Specifications

Brand	Integra
Item	Enclosure
Series	Premium
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/2/3/3R/3S/4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	12 x 10 x 6in (HxWxD)
Enclosure Height	12.54in
Enclosure Width	10.54in
Enclosure Depth	6.71in
Mounting	Wall

Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Polycarbonate
Color	Light gray
Finish	Gloss
Cover Type	Single-door
Latch Type	Glass-filled nylon quick-release latch
Padlock Attachment Type	Padlock hasp and staple
Padlockable	Yes
Keylocking	No
Includes	(2) mounting flanges

Agency Approvals

UL Listed File #	E207562
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/H12106HFNL-P10.pdf>
See store item page for other formats.