

H141206SF-P10 Cut Sheet



Integra Premium series enclosure, NEMA 1/2/3/3R/3S/4/4X/5/6/6P/12/13, 14 x 12 x 6in (HxWxD), wall mount, polycarbonate, gray, gloss finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H141206SF-P10>

Technical Specifications

Brand	Integra
Item	Enclosure
Series	Premium
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	1/2/3/3R/3S/4/4X/5/6/6P/12/13
IP Rating	IP68
Nominal Enclosure Dimensions	14 x 12 x 6in (HxWxD)
Enclosure Height	14.58in
Enclosure Width	12.58in
Enclosure Depth	7.04in

Mounting	Wall
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	Polycarbonate
Color	Gray
Finish	Gloss
Cover Type	Screw cover
Padlockable	No
Keylocking	No
Includes	(2) mounting flanges

Agency Approvals

UL Listed File #	E229365
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/H141206SF-P10.pdf>
See store item page for other formats.