

H2-PBC Cut Sheet



DL205 slave, (1) 9-pin D-sub female port(s), up to 10 Mbps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H2-PBC>

Technical Specifications

Brand	DL205
Item	Slave
Communication Port and Connection Type(s)	(1) 9-pin D-sub female
Port Protocol(s)	PROFIBUS DP
Port Speed(s)	up to 10 Mbps

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	E200031
CE	None
CSA File #	234884
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/H2-PBC.pdf>
See store item page for other formats.