

H20M040MD-M Cut Sheet



NITRA pneumatic cylinder, compact extruded, 20mm bore, 10mm rod diameter, 40mm stroke, double acting, magnetic piston, tapped end caps mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H20M040MD-M>

Technical Specifications

Brand	NITRA
Item	Cylinder
Working Fluid	Air
Cylinder Type	Compact extruded
Bore Diameter	20mm
Stroke	40mm
Port Size	M5 X 0.8 female threaded
Mounting	Tapped end caps
Action Type	Double acting
Magnetic Piston	Magnetic piston
Body Material	Anodized aluminum
Rod Material	Chrome-plated steel
Rod Diameter	10mm
Rod Thread Size	M5x0.8

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document