

H20RSSG0 Cut Sheet



WON H20 series standard bearing block, full ball recirculating bearing, rectangular, end seal and inside seal, carbon steel. For use with H20 series rails.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H20RSSG0>

Technical Specifications

Brand	WON	Dynamic Load Rating (C)	14900N
Item	Standard bearing block	Pitch Moment Load Rating (Mp)	221 N-m
Series	H20	Pitch Moment Load Rating, 2 Bearings (Mp2)	1049 N-m
Bearing Type	Full ball recirculating bearing	Yaw Moment Load Rating (My)	221 N-m
Block Type	Rectangular	Yaw Moment Load Rating, 2 Bearings (My2)	1049 N-m
Seal Type	End seal and inside seal	Roll Moment Load Rating (Mr)	251 N-m
Material	Carbon steel	For Use With	H20 series rails
Precision Class	Moderate precision		
Bearing Pre-load	Normal preload		
Mass	310g		
Static Load Rating (CO)	23900N		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/H20RSSG0.pdf>
See store item page for other formats.