

H4-ERM100 Cut Sheet



DirectLOGIC DL405 remote I/O module, 1 port, (1) Ethernet 10/100Base-T (RJ45) port(s). For use with all DL405 CPUs.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H4-ERM100>

Technical Specifications

Brand	DirectLOGIC
Item	Remote I/O module
Series	DL405
Number of Ports	1
Communication Port and Connection Type(s)	(1) Ethernet 10/100Base-T (RJ45)
Port Protocol(s)	<ul style="list-style-type: none">• IPX• TCP/IP• Ethernet remote I/O
Port Speed(s)	10/100 Mbps
For Use With	All DL405 CPUs
Programming Software	DirectSOFT programming software v4.0 or later

Agency Approvals

UL Listed File #	E185989
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/H4-ERM100.pdf>
See store item page for other formats.