

H401YF02Z1BF5 Cut Sheet



GC Valves solenoid valve, 2-port (2-way), 2-position, N.C., stainless steel body, Viton/PTFE seal(s), 1/4in female NPT inlet(s), 1/4in female NPT outlet(s), Cv=1.1, 0 psi minimum operating pressure, 120 VAC operating voltage, 18mm DIN style wiring plug.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H401YF02Z1BF5>

Technical Specifications

Brand	GC Valves
Item	Valve
Working Fluid	Air, inert gas, water or coolant
Valve Type	Solenoid process
Port Quantity	2-port (2-way)
Number Of Positions	2
Valve Configuration	N.C.
Action	Single solenoid spring return
Body Material	Stainless steel
Seal Material	Viton/PTFE
Inlet Port	1/4in female NPT
Outlet Port	1/4in female NPT
Flow Coefficient	1.1
Maximum Operating Pressure	2200 psi
Minimum Operating Pressure	0 psi
Working Fluid Temperature	230 deg F maximum
Operating Voltage	120 VAC
Power Rating	10 VA
Electrical Connection	18mm DIN style wiring plug

Agency Approvals

UL Listed File #	None
UL Recognized File #	YSY12 - MH17997
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR69111
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document