

H62922-1 Cut Sheet



Helukabel TrayControl 600 flexible control cable, unshielded, 3 conductors (includes ground), 16 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H62922-1>

Technical Specifications

Brand	Helukabel
Item	Cable
Series	TrayControl 600
Wire/Cable Type	Control
UL Wire/Cable Type	TC-ER, WTTC, DP-1, ITC-ER, PLTC-ER and MTW
Applicable Standards	NFPA 79, UL 1277, UL 2277 and ECOLAB
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V (Types TC, TC-ER, ITC-ER & PLTC-ER, MTW), 1000V (Type WTTC)
Conductors	3 conductors (includes ground)
Conductor Size	16 AWG
Conductor Stranding	26-stranded
Conductor Material	Bare copper

Conductor Insulation Material	PVC/Nylon
Conductor Insulation Color	Black with white numbers and green/yellow ground
Shielding	Unshielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	0.323in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 20 to 75ft = Coil• 76 to 375ft = 14 x 7in Reel• 376 to 535ft = 14 x 10in Reel• 536 to 820ft = 16 x 10in Reel• 821 to 1000ft = 18 x 10in Reel

Agency Approvals

UL Listed File #	E330430
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	257839
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document