

H62978-1 Cut Sheet



Helukabel TrayControl 600 flexible control cable, unshielded, 4 conductors (includes ground), 8 AWG, bare copper, PVC/Nylon conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H62978-1>

Technical Specifications

Brand	Helukabel	Conductor Insulation Color	Black with white numbers and green/yellow ground
Item	Cable	Shielding	Unshielded
Series	TrayControl 600	Jacket Material	PVC
Wire/Cable Type	Control	Jacket Color	Black
UL Wire/Cable Type	TC-ER, WTTC, DP-1 and MTW	Nominal Overall Cable Diameter	0.756in
Applicable Standards	NFPA 79, UL 1277, UL 2277 and ECOLAB	Bulk Length	Cut to length
Application	General purpose	Package Type	<ul style="list-style-type: none">• 20 to 30ft = Coil• 31 to 70ft = 14 x 7in Reel• 71 to 95ft = 14 x 10in Reel• 96 to 150ft = 16 x 10in Reel• 151 to 210ft = 18 x 10in Reel• 211 to 270ft = 18 x 13in Reel• 271 to 610ft = 24 x 17in Wooden Reel• 611 to 970ft = 30 x 17in Wooden Reel• 971 to 1000ft = Large Wooden Reel
Flexibility	Flexible		
Voltage Rating	600V (Types TC, TC-ER, MTW), 1000V (Type WTTC)		
Conductors	4 conductors (includes ground)		
Conductor Size	8 AWG		
Conductor Stranding	168-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	PVC/Nylon		

Agency Approvals

UL Listed File #	E330430
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	257839
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document