

# H63144-1 Cut Sheet



Helukabel TOPFLEX 600 VFD cable, shielded, 4 conductors (includes ground), 6 AWG, tinned copper, XLPE conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H63144-1>

## Technical Specifications

<b>Brand</b>	Helukabel
<b>Item</b>	Cable
<b>Series</b>	TOPFLEX 600
<b>Wire/Cable Type</b>	VFD
<b>UL Wire/Cable Type</b>	TC-ER and WTTC
<b>Applicable Standards</b>	UL 1277, UL 2277, UL 44 and ECOLAB
<b>Application</b>	Drive and motor
<b>Flexibility</b>	Flexible
<b>Voltage Rating</b>	600V (Type TC), 1000V (Type WTTC, Flexible Motor Supply Cable)
<b>Conductors</b>	4 conductors (includes ground)
<b>Conductor Size</b>	6 AWG
<b>Conductor Stranding</b>	266-stranded
<b>Conductor Material</b>	Tinned copper
<b>Conductor Insulation Material</b>	Cross linked polyethylene (XLPE)

<b>Conductor Insulation Color</b>	Black with white numbers and green/yellow ground
<b>Shielding</b>	Overall foil and braid shielded
<b>Jacket Material</b>	PVC
<b>Jacket Color</b>	Black
<b>Nominal Overall Cable Diameter</b>	0.972in
<b>Bulk Length</b>	Cut to length
<b>Package Type</b>	<ul style="list-style-type: none"><li>• 10 to 30ft = Coil</li><li>• 31 to 40ft = 14 x 7in Reel</li><li>• 41 to 60ft = 14 x 10in Reel</li><li>• 61 to 90ft = 16 x 10in Reel</li><li>• 91 to 125ft = 18 x 10in Reel</li><li>• 126 to 165ft = 18 x 13in Reel</li><li>• 166 to 370ft = 24 x 17in Wooden Reel</li><li>• 371 to 590ft = 30 x 17in Wooden Reel</li><li>• 591 to 1000ft = Large Wooden Reel</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E330430
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	257839
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>