

H63146-1 Cut Sheet



Helukabel TOPFLEX 600 VFD cable, shielded, 4 conductors (includes ground), 2 AWG, tinned copper, XLPE conductor insulation material, black with white numbers and green/yellow ground, PVC jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H63146-1>

Technical Specifications

Brand	Helukabel
Item	Cable
Series	TOPFLEX 600
Wire/Cable Type	VFD
UL Wire/Cable Type	TC-ER and WTTC
Applicable Standards	UL 1277, UL 2277, UL 44 and ECOLAB
Application	Drive and motor
Flexibility	Flexible
Voltage Rating	600V (Type TC), 1000V (Type WTTC, Flexible Motor Supply Cable)
Conductors	4 conductors (includes ground)
Conductor Size	2 AWG
Conductor Stranding	665-stranded
Conductor Material	Tinned copper
Conductor Insulation Material	Cross linked polyethylene (XLPE)

Conductor Insulation Color	Black with white numbers and green/yellow ground
Shielding	Overall foil and braid shielded
Jacket Material	PVC
Jacket Color	Black
Nominal Overall Cable Diameter	1.252in
Bulk Length	Cut to length
Package Type	<ul style="list-style-type: none">• 10 to 20ft = Coil• 21 to 25ft = 14 x 7in Reel• 26 to 35ft = 14 x 10in Reel• 36 to 55ft = 16 x 10in Reel• 56 to 75ft = 18 x 10in Reel• 76 to 100ft = 18 x 13in Reel• 101 to 220ft = 24 x 17in Wooden Reel• 221 to 355ft = 30 x 17in Wooden Reel• 356 to 500ft = Large Wooden Reel

Agency Approvals

UL Listed File #	E330430
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	257839
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document