

HBP14C15CBL-QC Cut Sheet



NITRA pneumatic coiled hose, polyurethane, polyester reinforced, clear blue, 1/4in inside diameter, 0.375in outside diameter, 1/4in chrome plated steel quick-disconnect fittings, 12ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HBP14C15CBL-QC>

Technical Specifications

| | |
|------------------------------|-----------------------------------------------------|
| Brand | NITRA |
| Item | Pneumatic Coiled hose |
| Material | Polyurethane |
| Reinforcement | Polyester |
| Color | Clear blue |
| Inside Diameter | 1/4in |
| Outside Diameter | 0.375in |
| Connection | 1/4in chrome plated steel quick-disconnect fittings |
| Working Length | 12ft working length |
| Operating Pressure | 310 psi |
| Operating Temperature | -40 to +120 deg F |

Agency Approvals

| | |
|-----------------------------|----------------------------------------|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |