

# HBP38C15CBL-QC Cut Sheet



NITRA pneumatic coiled hose, polyurethane, polyester reinforced, clear blue, 3/8in inside diameter, 0.5625in outside diameter, 3/8in chrome plated steel quick-disconnect fittings, 12ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HBP38C15CBL-QC>

## Technical Specifications

<b>Brand</b>	NITRA
<b>Item</b>	Pneumatic Coiled hose
<b>Material</b>	Polyurethane
<b>Reinforcement</b>	Polyester
<b>Color</b>	Clear blue
<b>Inside Diameter</b>	3/8in
<b>Outside Diameter</b>	0.5625in
<b>Connection</b>	3/8in chrome plated steel quick-disconnect fittings
<b>Working Length</b>	12ft working length
<b>Operating Pressure</b>	310 psi
<b>Operating Temperature</b>	-40 to +120 deg F

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>