


HBP38C15CBL Cut Sheet



NITRA pneumatic coiled hose, polyurethane, polyester reinforced, clear blue, 3/8in inside diameter, 0.5625in outside diameter, 3/8in male NPT brass fittings (one end fixed, one end swivel), 12ft working length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HBP38C15CBL>

Technical Specifications

Brand	NITRA
Item	Coiled hose
Working Fluid	Air or inert gas
Material	Polyurethane
Reinforcement	Polyester
Color	Clear blue
Inside Diameter	3/8in
Outside Diameter	0.5625in
Connection	3/8in male NPT brass fittings (one end fixed, one end swivel)
Working Length	12ft working length
Operating Pressure	310 psi
Operating Temperature	-40 to +120 deg F

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/HBP38C15CBL.pdf>
See store item page for other formats.