

HBVPB-11L-WNL Cut Sheet



Bimed pressure relief vent plug, M12 x 1.5mm thread type, polyamide, light gray, 2,000 mL/min @ 70 mBar (1 psi), IP67 IP68, UL Type 4X, 12 and 13. Package of 2.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HBVPB-11L-WNL>

Technical Specifications

Brand	Bimed
Item	Pressure relief vent plug
Thread Type	M12 x 1.5mm
Thread Length	10mm
Material	Polyamide
Color	Light gray
Free Airflow	2,000 mL/min @ 70 mBar (1 psi)
Water Intrusion Pressure	0.2 bar (3 psi)
IP Rating	IP67 IP68
Operating Temperature	-20 to +100 deg C
UL Type	4X, 12 and 13
Quantity per Pack	2
Includes	Washer and lock nut
Additional Information	Use 17mm wrench size

Agency Approvals

UL Recognized File #	E350312
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/HBVPB-11L-WNL.pdf>
See store item page for other formats.