

# HC-1-193002 Cut Sheet



IDEM safety switch, solid shaft hinge interlock, slow action, (2) N.C. safety output(s), plastic body, 316 stainless steel head, 10mm diameter x 80mm length shaft, (1) 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HC-1-193002>

## Technical Specifications

|                           |                                   |
|---------------------------|-----------------------------------|
| <b>Brand</b>              | IDEM                              |
| <b>Item</b>               | Safety switch                     |
| <b>Actuator Type</b>      | Solid shaft hinge interlock       |
| <b>Head Type</b>          | 90-degree adjustable              |
| <b>Action</b>             | Slow action                       |
| <b>Safety Output Type</b> | (2) N.C.                          |
| <b>Housing Size</b>       | 25 x 77 x 29mm                    |
| <b>Body Material</b>      | Plastic                           |
| <b>Head Material</b>      | 316 stainless steel               |
| <b>Shaft Size</b>         | 10mm diameter x 80mm length shaft |
| <b>IP Rating</b>          | IP67                              |
| <b>Connection</b>         | (1) 4-pin M12 quick-disconnect    |
| <b>Cable Length</b>       | 9.8in/250mm                       |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E258676                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |