

HC-58 Cut Sheet



NITRA hose clamp, 2-ear, 0.748-0.906in diameter, plated steel.
Package of 10. For use with HBV series 5/8in hose.

For complete product information, please see this item on our
store at the following link:



<https://www.automationdirect.com/pn/HC-58>

Technical Specifications

| | |
|-------------------|-----------------------|
| Brand | NITRA |
| Item | Hose clamp |
| Clamp Style | 2-ear |
| Clamp Range | 0.748-0.906in |
| Material | Plated steel |
| Quantity per Pack | 10 |
| For Use With | HBV series 5/8in hose |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |