

# HC14-14F-C Cut Sheet



NITRA pneumatic quick disconnect fitting, automatic coupling, chrome-plated steel body, (1) 1/4in female NPT to (1) 1/4in universal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HC14-14F-C>

## Technical Specifications

|                          |  |
|--------------------------|--|
| Brand                    | NITRA  |
| Item                     | Fitting                                      |
| Working Fluid            | Air or inert gas                             |
| Fitting Connection Type  | Quick disconnect                             |
| Fitting Type             | Automatic coupling                           |
| Body Material            | Chrome-plated steel                          |
| Fitting Measurement Type | SAE  |
| Connection               | (1) 1/4in female NPT and (1) 1/4in universal |
| Operating Pressure       | 150 psi                                      |
| Operating Temperature    | 32 to 150 deg F                              |

## Agency Approvals

|                      |  |
|----------------------|--|
| UL Listed File #     | None                                   |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |