

# HC3096N-48-900-24 Cut Sheet



Dold force guided relay, 35mm DIN rail mount, finger-safe, 24 VDC coil voltage, 4PST, (3) N.O., (1) N.C., 5A contact rating, 10-pin, LED indicator(s), diode protection.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HC3096N-48-900-24>

## Technical Specifications

Brand	Dold
Item	Relay
Relay Type	Force guided
Mounting	35mm DIN rail
Relay Housing Type	Finger-safe
Coil Voltage	24 VDC
Relay Configuration	4PST
Output Type	(3) N.O., (1) N.C.
Contact Rating	5A
Connector Type	10-pin
Indicator	LED
Protection Type(s)	diode

## Agency Approvals

UL Listed File #	E146415
UL Recognized File #	None
UL Hazardous File #	None
CE	<a href="#">View CE declarations</a>
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HC3096N-48-900-24.pdf>  
See store item page for other formats.