

HC38-38F-A Cut Sheet



NITRA pneumatic quick disconnect fitting, coupling, steel body, (1) 3/8in female NPT to (1) 3/8in industrial interchange.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HC38-38F-A>

Technical Specifications

| | |
|--------------------------|---|
| Brand | NITRA |
| Item | Fitting |
| Working Fluid | Air or inert gas |
| Fitting Connection Type | Quick disconnect |
| Fitting Type | Coupling |
| Body Material | Steel |
| Fitting Measurement Type | SAE |
| Connection | (1) 3/8in female NPT and (1) 3/8in industrial interchange |
| Operating Pressure | 150 psi |
| Operating Temperature | 32 to 150 deg F |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |